

Quality, Simplicity and Safety at an Affordable Price



Hill-Rom® 405 Electric Bed
Hill-Rom® 305 Manual Bed

Hill-Rom


Enhancing Outcomes for Patients and Their Caregivers.™

The Hill-Rom® 305 and 405 beds are designed to provide the quality of construction, simplicity of use and safety compliance you expect in a bed from Hill-Rom®. The 405 electric bed and 305 manual bed are your best value options for general care procedures.

Designed for Safety

The 305 and 405 beds incorporate the essential safety features to keep patients on the recovery path.

- New siderail design shields the patient, to help prevent patient entrapment and falls
- One step head board removal for rapid access to the patient's head
- Trend and reverse Trend for emergency situations and comfort
- Zero-gap allows safe and easy patient transfers
- CPR quick release handle ergonomically located at the headend of the 405 electric bed and foot end on the 305 manual bed
- Electrical function lock out controls (405 electric bed)



Designed for Simplicity

The Hill-Rom® 305 and 405 beds have an open-architecture design which allows for quick and easy cleaning, helping to reduce the risk of infection. The intuitive controls make it easy to use.


- Embedded Patient and Caregiver siderail controls (405 electric bed)
- Brake and steer pedals accessible from all four corners of the bed
- Angle indicator for Trend and Reverse Trend
- Battery Back up solution (405 electric bed)
- Automatic contouring sleep deck to prevent patients from slipping to the foot end of the bed
- Optional Radiolucent backrest for easy and safe X-rays



Four corner central brake and steer



Battery back-up (405 electric bed)




Radiolucent backrest (optional)

Designed for Quality

Meets international quality and safety standards

- IEC 60601-1 Medical Electrical Equipment: General Requirements for Safety
- IEC 606 01-1-2 Top level standard for electromagnetic compatibility for electrical medical equipment.
- IEC 60601-2-38 Requirements for safety of a hospital bed such as construction, mechanical strength, mechanical hazards, protection against fluid ingress, and essential performance.
- UL 60601 Base standard for electro medical equipment
- IXP 4 Level of protection against ingress of fluid
- CE Mark European marking of conformity that indicates that a product complies with the essential requirements of the applicable European laws or Directives.

“The Hill-Rom® 305 and 405 beds are designed to provide the quality of construction, simplicity of use and safety compliance you expect from Hill-Rom®.”



Technical Data:

Bed Length with Standard sleep deck.....	90.0" (228.6 cm)	Knee Section Articulation.....	0 through 25°
Bed Length with Special sleep deck.....	87.0" (221.0 cm)	Caster Size.....	5.0" (13.0 cm)
Width (with siderails up).....	43.7" (110.9 cm)	Safe Working Load.....	450 lbs. (204 kg)
Width (with siderails down).....	36.6" (93.0 cm)	Operable Temperature Range*.....	+10° C to +40° C
Height of Sleep Deck (in low position).....	18.3" (46.5 cm)	Operable Relative Humidity Range**	30% to 95% non-condensing
Height of Sleep Deck (in high position).....	30.1" (76.5 cm)		
Underbed Clearance.....	5.5" (13.9 cm)		
Head Section Articulation.....	0 through 72.5°		

* Product withstands storage/transportation in temperature range of -40° C to +70° C

** Product withstands storage/transportation in relative humidity range of 10% to 95%



Enhancing Outcomes for Patients and Their Caregivers.™

France +33 (0)2 97 50 92 12
 United Kingdom +44 (0)1530 411000
 Deutschland 0800 8 63 55 37
 Nederland +31 (0)347 32 35 32
 Italia + 39 (0)2 950541
 Suisse/Schweiz +41 (0)21 706 21 30
 (deutschsprachig) 0800 8 63 55 37

Österreich 0800 8 63 55 37
 Ireland +353 (0)1 413 6005
 Iberia +34 (0)93 6856000
 Nordic Countries +46 (0)20 78 10 30
 Export Contact your local Hill-Rom distributor or contact your Area Manager via website or call +1 812 934 8173

www.hill-rom.com

Hill-Rom® reserves the right to make changes without notice in design, specifications and models. The only warranty Hill-Rom® makes is the express written warranty extended on the sale or rental of its products.
 © 2013 Hill-Rom® SARL, ALL RIGHTS RESERVED.